



PE175BF and PE175BUV **CERMAX® XENON ARC LAMPS**



Cermax Xenon short arc lamps from Excelitas are ideal for applications that require a high degree of illumination control.

The Cermax® Xenon short arc lamp from Excelitas Technologies is an innovative lamp design in the specialty lighting industry. Cermax Xenon lamps were introduced in the early 1980s and are now used in diagnostic and surgical endoscopes in most major hospitals worldwide, in high brightness projection display systems, and for a wide variety of other high- performance applications.

Model PE175BF and PE175BUV lamps, have an integrated parabolic reflector, enabling high intensity, focused light output. Due to the Xenon lamp's broad color spectrum, the lamp is filtered to emit ultraviolet, visible, or infrared radiation, depending upon application and usage. With their internal reflector and rugged ceramic body construction, Cermax lamps are the safest and most compact alternative to conventional quartz xenon lamps. Cermax lamps are ideal for applications that require a high degree of illumination control.

Current-regulated or power-regulated power supplies with output ripples of less than 5% are recommended. Single shot ignition pulses are advised because radio frequency starters may damage the lamps internal reflector.

In addition to lamps, Excelitas Technologies manufactures power supplies for Cermax Xenon arc lamps, lamp holders, OEM lighting systems, and fiber optic light sources.

www.excelitas.com

PE175BF 11/2011 page 1 of 4

CERMAX

Key Features

- High Intensity illumination - 2200 Lumens
- Up to 3.5 watts of UV output (<390nm)
- Power range of 150-200 watts
- 1000 hours life
- Broad spectral range with 5900 Kelvin color temperature

Applications

- Medical and industrial fiber optic illuminators
- Machine vision
- Infrared and visible spotlights/beacons
- Spectroscopy
- Microscopy
- UV Curing
- Video projection

EXCELITAS
TECHNOLOGIES

PE175BF and PE175BUV

CERMAX® XENON ARC LAMPS

PE175BF and PE175BUV

Operational Specifications		
Description	Nominal	Range
Power	175 Watts	150-200 watts
Current	14 amps (DC)	12-16 amps (DC)
Operating Voltage	12.5 volts (DC)	11-14 volts (DC)
Ignition Voltage	23 kilovolts (recommended minimum)	
Temperature	150° C (Maximum)	
Lifetime*	1000 hours typical	

* End of life is defined as 50% of initial output

Initial Output at Nominal Power		
F= UV Filtered Output	UV= UV Enhanced Output	
Description	PE175BF	PE175BUV
Peak Intensity	350x10 ³ candelas	330x10 ³ candelas
Radiant Output*	25 watts	25 watts
UV Output*	1.2 watts	3.5 watts
IR Output*	14 watts	13 watts
Visible Output*	2200 Lumens	2000 Lumens
Color Temperature	5900 Kelvin	5050 Kelvin
Peak Instabilities	4%	4%
Beam Geometry**	4.5°/5°/6°	

* These values indicate total output in all directions. Wavelengths = UV<390nm, IR>770nm, Visible: 390nm-770nm

** Beam Geometry defined as the half angle at 10% PTS after 01/100/1000 hours

Physical Specifications	
Description	Specification
Arc Gap	0.045 inch (1.14 mm)
Reflector Geometry	Parabolic Y ² = 0.5 X (inch)
Weight	131 grams
Window Diameter	1.0 inch (25.4 mm)

PE175BF and PE175BUV

CERMAX® XENON ARC LAMPS

PE175BF


Focused Output with a F/1.0 Lens		
Description	Visible Output	Total Output*
3 mm aperture	830 Lumens	8 watts
6 mm aperture	1400 Lumens	13 watts

* Nominal values at 175 watts after 2 hour burn-in.

NOTES:

1. Lamp must not be operated with window facing upwards within 45° of vertical.
2. Seal temperature must not exceed 150° C.
3. Current/power regulated power supplies and Excelitas lamp housing units are recommended.
4. Lamp must be operated within recommended current and power range. Over powering may lead to arc instability, hard starting and premature aging.
5. Hot mirror assembly is available for IR filtering.
6. CERMAX lamps are much safer lamps to use than their quartz xenon arc lamp equivalents. However, caution must be practiced when operating lamps because they are under high pressure, require high voltage, reach temperatures up to 200° C, and their IR and UV radiation can cause skin burns and eye damage. Read hazard sheet included with each lamp shipment.


Mechanical Dimensions



PE175BF and PE175BUV
CERMAX® XENON ARC LAMPS

Spectral Output

PE175BF and PE175BUV



About Excelitas Technologies

Excelitas Technologies is a global technology leader focused on delivering innovative, customized solutions to meet the lighting, detection and other high-performance technology needs of OEM customers.

From aerospace and defense applications to medical lighting, analytical instrumentation, clinical diagnostics, industrial, and safety and security applications, Excelitas Technologies is committed to enabling our customers' success in their specialty end-markets. Excelitas Technologies has approximately 3,000 employees in North America, Europe and Asia, serving customers across the world.

Excelitas Technologies Illumination, Inc.
 44370 Christy Street
 Fremont, California
 94538-3180 USA
 Telephone: (+1) 510.979.6500
 Toll-free: (+1) 800.775.6786
 Fax: (+1) 510.687.1140
 shortarcxenon.na@excelitas.com

Excelitas Technologies Singapore, Private Limited.
 47 Ayer Rajah Crescent #06-12
 Singapore 139947
 Telephone: (+65) 6775 2022 (Main Line)
 Telephone: (+65) 6770 4366
 (Customer Service Hotline)
 Fax: (+65) 6778-1752
 shortarcxenon.asia@excelitas.com

Excelitas Technologies GmbH & Co. KG
 Wenzel-Jaksch-Str. 31
 D-65199 Wiesbaden
 Germany
 Telephone: (+49) 611 492 430
 Fax: (+49) 611 492 165
 shortarcxenon.europe@excelitas.com

Japan Excelitas Technologies
 East Tower 4th Floor,
 Otemachi First Square
 1-5-1 Otemachi, Chiyoda-ku,
 Tokyo 100-0004
 Telephone: (+81) 3-5219-1228
 Fax: (+81) 3-5219-1201

For a complete listing of our global offices, visit www.excelitas.com/locations

© 2012 Excelitas Technologies Corp. All rights reserved. The Excelitas logo and design are registered trademarks of Excelitas Technologies Corp. All other trademarks not owned by Excelitas Technologies or its subsidiaries that are depicted herein are the property of their respective owners. Excelitas reserves the right to change this document at any time without notice and disclaims liability for editorial, pictorial or typographical errors.

